

# Kolorimeter

The PowerMon Kolorimeter is a versatile applicable on-line measuring instrument. It guarantees a permanent optimal water quality by the continuous supervision of the legally prescribed limit value for total phosphate and ortho-phosphate in the outlet of municipal and industrial purification plants.

Apart from higher precision and shortening of the measuring cycles, the PowerMon offers a special highlight: For the measurement of most diverse parameters (e.g. oxygen, pH, redox, conductivity etc.) the connection of various sensors is possible!

For the individual sensors the PowerMon automatically takes over the functions of a transducer. It is also possible to set the separate results against each other.

A remote supervision enables the permanent control of the correct function of your plant. The highest possible data transfer over the interfaces, as well as the operation of the PowerMon via the touch screen user interface ensures an easy and user friendly operation.

## Applications

- Aluminium and manganese in drinking water treatment
- Phosphate in waste water
- Cyanide in steel mills
- Nitrate in river water
- and others

**In North America:**



[www.southforkinstruments.com](http://www.southforkinstruments.com)



## Advantages

- precise results
- connection of external physical sensors and actuators
- fully automatic operation
- easy, comfortable operation
- fast data transfer
- self-monitoring system
- remote maintenance and network ability
- graphic user interface with interactive Touch Screen operation
- update of the operating software or download of data by USB stick
- minimum operating cost by small reagent consumption
- second measuring point without surcharge
- operation also possible without housing

# PowerMon Kolorimeter



The compact and modular design of the PowerMon can contain up to six on-line measuring points in one device and enables a space-saving and economic operation



## Technical Data

### MEASURING METHODS

cyclic, colorimetric

### MEASURING CYCLE

typ. 10 - 15 min.

### MEASURING RANGE

PO4

3- 0 - 0,5/6,0 mg/l

Cl<sub>2</sub> 0 - 0,2/3,0 mg/l

Fe 0 - 0,2/3,0 mg/l

Al 0 - 0,1/1,0 mg/l

Mn 0 - 0,1/2,0 mg/l

Cu 0 - 0,03/1,0 mg/l

Further parameters and measuring ranges on request

### PRECISION

depending on the application\*

### DRIFT

depending on the application\*

Number of measuring points

max. 6

### OUTPUT SIGNAL

0/4-20 mA

max. load 500 OHM

characteristic curve:

linear/logarithmic

galvanically isolated

### INTERFACES

USB / Ethernet

Option:

modem: analog, GSM, ISDN,

UMTS

Profibus DP, Modbus RTU

### RELAY CONTACTS

4/12 potential free contacts

free allocable

(e.g. alarm contact)

### DIGITAL INPUTS

4/12 e.g. activating and deactivating of measuring points, system control

### SAMPLE

pressure-free

Temperature : 15 - 45°C

(288 - 318 K)

Flow : 3 - 10 l/h

free from suspended matter and oil

Connection : tube, flexible

(ID 1.5 - 3 mm)

### DRAIN

pressure-free

tube, flexible

(ID 10 mm)

### POWER SUPPLY

85...264 VAC at

47...63 Hz

Power consumption

max. 150 VA

### ENVIRONMENTAL TEMPERATURE

15 - 35°C (288 - 308 K)

### INSTALLATION

wall-mounted

### PROTECTION CLASS (EN 60529)

IP 65 (electronics)

IP 54 (with housing)

IP 21 (with jacket)

### WEIGHT

housing with reagent cabinet

53 - 60 kg without reagents

### DIMENSIONS

(HEIGHT X WIDTH X DEPTH)

housing: 700x600x320 mm

with reagent cabinet:

1100x600x354 mm

For further information please contact our Technical Support Department

**SPX**

NORTH AMERICA DISTRIBUTION



www.southforkinstruments.com

SPX Flow Technology Norderstedt GmbH - Werkstraße 4 - D-22844 Norderstedt  
Phone: +49 40 52202-0 Fax: +49 40 52202-444 E-Mail: branluebbe@spx.com

SPX reserves the right to incorporate our latest design and material changes without notice or obligations.

Design features, materials of construction and dimensional data, as described in this bulletin, are provided for your information only and should not be relied upon unless confirmed in writing. Please contact your local sales representative for product availability in your region. For more information visit [www.spx.com](http://www.spx.com).

"The green ">" is a trademark of SPX Corporation, Inc."