

EXstatic 311 TriClamp connection




- » Designed according to hygienic criteria
- » Surface finish $Ra < 0,78$ or $Ra < 0,37$
- » Stainless steel AISI 316L / 1.4404
- » EPDM sealings with FDA and USP VI approval
- » Optional sensor protection cage
- » Up to 10 bar and 140 °C
- » Protection cap for cable connection

Static sensor holder with TriClamp connection for permanent installation of Ø12mm/120mm-sensors in tanks or pipes

Specifications

max. pressure	10 bar
max. temperature	140°C
material	1.4404 / 316L
surface	$Ra < 0,78$ or $Ra < 0,37$
sealing material	EPDM / FDA / USP VI or FPM (Viton)
material cable guard	PA6.6 GF30
certificates	material, surface, sealing material
option	with protection cage or without protection cage
sensors	120mm / PG13,5
process connection	TriClamp 1.5" (Ø50,5) or TriClamp 2" (Ø64)

Dimensions



EXstatic 311 TriClamp connection



EXstatic 311 - version without protective cage



EXstatic - installation situation from inside



Version with protective cage

Ordercode

Code	Material (wetted parts)	Delivery
0408	Stainless Steel 1.4404 / 316L Ra0,78	2 weeks
0404	Stainless Steel 1.4404 / 316L Ra0,37	4 weeks

Code	Sealing Material (wetted sealings)	Delivery
EPD	EPDM/FDA/USP VI	2 weeks
FPM	FPM (Viton)	2 weeks

Code	Sensor type	Delivery
120	120mm PG 13,5 Ø12mm	2 weeks

Code	Process Connection	Delivery
TC15	TriClamp 1-1,5" (OD Ø50.5mm)	2 weeks
TC20	TriClamp 2.0 (OD Ø64mm)	2 weeks

Code	Immersion length	Delivery
045	45mm under process connection	2 weeks
080	80 mm under process connection	2 weeks

Code	Protection cage	Delivery
0	without	2 weeks
1	with protection cage	2 weeks